

NEMA Plug Chart – Straight

rev 20100615

		15 AMPERE		20 AMPERE		30 AMPERE		50 AMPERE		60 AMPERE	
		RECEPTACLE	PLUG	RECEPTACLE	PLUG	RECEPTACLE	PLUG	RECEPTACLE	PLUG	RECEPTACLE	PLUG
2-POLE 2-WIRE	125V	 1-15R	 1-15P								
	250V		 2-15P	 2-20R	 2-20P	 2-30R	 2-30P				
	277V										
	600V										
2-POLE 3-WIRE GROUNDING	125V	 5-15R	 5-15P	 5-20R	 5-20P	 5-30R	 5-30P	 5-50R	 5-50P		
	250V	 6-15R	 6-15P	 6-20R	 6-20P	 6-30R	 6-30P	 6-50R	 6-50P		
	277V AC	 7-15R	 7-15P	 7-20R	 7-20P	 7-30R	 7-30P	 7-50R	 7-50P		
	347V AC	 24-15R	 24-15P	 24-20R	 24-20P	 24-30R	 24-30P	 24-50R	 24-50P		
	480V AC										
	600V AC										
3-POLE 3-WIRE	125/250V			 10-20R	 10-20P	 10-30R	 10-30P	 10-50R	 10-50P		
	3Ø 250V	 11-15R	 11-15P	 11-20R	 11-20P	 11-30R	 11-30P	 11-50R	 11-50P		
	3Ø 480V										
	3Ø 600V										
3-POLE 4-WIRE GROUNDING	125/250V	 14-15R	 14-15P	 14-20R	 14-20P	 14-30R	 14-30P	 14-50R	 14-50P	 14-60R	 14-60P
	3Ø 250V	 15-15R	 15-15P	 15-20R	 15-20P	 15-30R	 15-30P	 15-50R	 15-50P	 15-60R	 15-60P
	3Ø 480V										
	3Ø 600V										
4-POLE 4-WIRE	3ØY 120/208V	 18-15R	 18-15P	 18-20R	 18-20P	 18-30R	 18-30P	 18-50R	 18-50P	 18-60R	 18-60P
	3ØY 277/480V										
	3ØY 347/600V										
4-POLE 5-WIRE GNDG	3ØY 120/208V										
	3ØY 277/480V										
	3ØY 347/600V										