

LOCAL CONSOLE CONTROLLER



CONTROLS LOCAL AND REMOTE ACCESS

Raritan's Local Console Controller LCC-USB-VGA is a console switch device which allows two consoles to access a single computer on a first-come, first-serve basis. An alternate version, the LCC-USB-VGA-6MC is available with a cable to connect to an external switch.

LCC-USB-VGA is designed for manufacturing and factory environments. Connected to single computer or manufacturing device, the LCC controls local and remote access to allow both remote and local access, or for safety purposes, to disconnect remote access when undergoing local maintenance or local use.

FRONT VIEW (CONSOLE SIDE)



| No. | Port Name | |
|-----|-----------------------|--|
| 1 | Push button and reset | |
| 2 | Video out for C1 | |
| 3 | USB hub for KB/MS | |
| 4 | Video out for C2 | |
| 5 | USB hub for KB/MS | |

REAR VIEW (PC SIDE)



| No. | Port Name | |
|-----|-------------------------------|--|
| 6 | Mini DIN (dry contact) | |
| 7 | PC port (combo free cable) | |
| 8 | DIP switch (function setting) | |
| 9 | Mini USB (firmware upgrade) | |
| 10 | DC jack | |

KEY FEATURES

- Two USB-VGA consoles control a single computer
- Automatic computer sharing on firstcome first-serve basis
- Supports PS/2 and USB computers
- Supports console switching via push button and hot-key
- PC share or manual operation mode selection
- Configurable DIP switches
- Option for Private Mode
- Rackmountable
- Supports dry contact by I/O Port
- Status LED
- Firmware upgradeable
- Supports VGA, SVGA and MultiSync monitors
- Multi-platform support
- Compatible with Raritan Dominion KX III




| Function | LCC-USB-VGA | LCC-USB-VGA | | |
|------------------------------|--|---|-------------------------------|--|
| Console Connections | 2 | | | |
| Computer Connections | 1 | | | |
| Console Selection | Hot-key, push button | | | |
| Connectors | Console port | Keyboard | 2 x USB Type A female (white) | |
| | | Mouse | 2 x USB Type A female (white) | |
| | | Video | 2 x HDB15 female (blue) | |
| | Computer port | | 1 x HDB15 female (black) | |
| | Power supply | | 1 x DC jack | |
| | Firmware upgrade | | 1 x Mini USB female | |
| | I/O port (dry contact max. AC125V/0.51A, DC 60W) | | 1 x 6-pin Mini DIN (black) | |
| | Operation mode selection | | 1 x Push button (red) | |
| Switch | Reset | | 1 x Mush button (rea) | |
| | DIP | | 1 x 4-pin (blue) | |
| LEDs | PC share | | 1 x Yellow | |
| LEUS | User selected | | 2 x green | |
| Video Resolution | 1920 x 1440 @ 60Hz, DDC2B | | | |
| Console Free Timeout Setting | 10 / 60 / 180 / 300 Seconds | | | |
| Power Consumption | DC 5V / 2A | | | |
| Environment | Operating temperature | 0°-50° C; 32°-122° F | | |
| | Storage temperature | -20°-60° C; -4°-140° F | | |
| | Humidity | 0–80% RH, non-condensing | | |
| Physical | Housing | Metal | | |
| | Weight | 350g; 12.346 oz | | |
| | Dimensions (L x W x H) | 135 mm x 84 mm x 29 mm; 5.31" x 3.30" x 1.14" | | |
| Safety | CE/FCC/VCCI | | | |

| Package Contains | | |
|--|----------|--|
| Description | Quantity | |
| Local Console Controller LCC-USB-VGA | 1 | |
| 1.8M Combo Free Cable | 1 | |
| Universal DC 5V 2A universal Power Adapter | 1 | |
| Quick Installation Guide | 1 | |

| Ordering Information | | |
|--------------------------|-------------|--|
| Description | Part Number | |
| Local Console Controller | LCC-USB-VGA | |

| Cable Option | | | |
|--|-------------|--|--|
| Description | Part Number | | |
| All-in-one KVM Cable 1.8M (PS/2+USB+VGA) | EZCBL-18 | | |
| All-in-one KVM Cable 3M (PS/2+USB+VGA) | EZCBL-20 | | |



Visit www.raritan.com/ap/kxiii

©2018 Raritan Inc. All rights reserved. Raritan® is a registered trademarks of Raritan Inc. or its wholly-owned subsidiaries. All others are registered trademarks or trademarks of their respective owners. Raritan began developing KVM switches for IT professionals to manage servers remotely in 1985. Today, as a brand of Legrand, we are a leading provider of intelligent rack PDUs. Our solutions increase the reliability and intelligence of data centers in 9 of the top 10 Fortune 500 technology companies. Learn more at Raritan.com **V1255**

