

	RARITAN PDU	INPUT PLUG TYPE	MAX CURRENT	FORM FACTOR	OUTLET SWITCHING	INLET METERING	OUTLET METERING	TOTAL METERING	C13	C19
VOLTAGE: 400 V, 3Ø	PX3-1730V-V2	IEC 60309	32A	0U		✓		36	24	12
	PX3-1732	IEC 60309	16A	0U		✓		36	24	12
	PX2-2730	IEC 60309	32A	0U	✓	✓		36	24	12
	PX2-4104R-V2	IEC 60309	32A	1U		✓		6		6
	PX3-5530V	IEC 60309	32A	0U	✓	✓	✓	24	21	3
	PX3-5730-V2	IEC 60309	32A	0U	✓	✓	✓	36	24	12
VOLTAGE: 230 V, 1Ø	PX2-1190R	IEC 60309	16A	1U		✓		8	8	
	PX3-1493V	IEC 60309	32A	0U		✓		24	20	4
	PX2-2190CR	IEC 60320 C20	16A	1U	✓	✓		8	8	
	PX2-2190R	IEC 60309	16A	1U	✓	✓		8	8	
	PX2-2486	IEC 60309	16A	0U	✓	✓		24	24	
	PX2-2488	IEC 60309	16A	0U	✓	✓		24	20	4
	PX2-2493	IEC 60309	32A	0U	✓	✓		24	20	4
	PX3-5190CR	IEC 60320 C20	16A	1U	✓	✓	✓	8	8	
	PX3-5190R	IEC 60309	16A	1U	✓	✓	✓	8	8	
	PX3-5260R	IEC 60309	16A	1U	✓	✓	✓	12	12	
	PX3-5493V	IEC 60309	32A	0U	✓	✓	✓	24	20	4