



Control 2 to 8 PCs from one keyboard, monitor, and mouse.

CompuSwitch

Connect any mix of PCs (PS/2® or AT), Sun®, and Mac®, running any operating system. Raritan's unique keyboard and mouse emulation ensures flawless operation.

Cascade CompuSwitch units to control up to 64 computers.

CS2 – 2 Port

CS4 – 4 Port

CS8 – 8 Port

CS4R – 4 Port

Rack mount with cable support bracket

CS8R – 8 Port

Rack mount with cable support bracket

The perfect switch for desktop or rack mount installations

The Raritan family of KVM (keyboard, video, mouse) switch products provides reliable, central control of multiple computers for the simplest to the most complex requirements. CompuSwitch is Raritan's economical, multi-platform, single-user KVM switch and is available with models for 2, 4, and 8 computers, expandable to control up to 64 computers. Its industrial strength, desktop and rack mount chassis makes CompuSwitch an ideal choice for corporate server rooms, computer test labs, and rack mount applications. CompuSwitch helps eliminate the cost and clutter of unnecessary equipment, reclaim space, improve operational productivity for a host of applications:

- ▶ Network server management.
- ▶ Multi-workstation operation.
- ▶ Hardware/software development and testing labs.
- ▶ CTI and other OEM rack mount applications.

Premium performance and reliability

CompuSwitch is built with Raritan's unique, intelligent emulation technology, which dedicates an individual processor to each connected computer so that each computer always sees its own keyboard and mouse. This prevents keyboard and mouse lockups and ensures flawless boot up and operation of any mix of computers running any operating system.

CompuSwitch is available in 2-port, 4-port, and 8-port models. Connect any mix of PCs (PS/2 or AT), Sun, and Mac, running any operating system and cascade CompuSwitch units to control up to 64 computers. Raritan's unique keyboard and mouse emulation ensures flawless operation.

Installation is as easy as connecting computers with our tangle-proof, coaxial, ultra thin, double-shielded KVM cables, available in lengths of 0.6, 2, 4, 6, and 9m. Simply plug in your keyboard, monitor, and mouse to operate.

Selection of computers is done directly by touching the individual port buttons on the front panel of CompuSwitch, or by using hot-key commands from the keyboard. Standard features like AutoScan and AutoSkip make operation simple and convenient.



CS8R (Rack-mount chassis)

CompuSwitch 4 and 8-port models are also available in a 1U, industrial-strength, rack-mount chassis with a built-in cable support bracket for a neat, professional installation.

Features

- ▶ High reliability, low cost, easy to use.
- ▶ 2-port, 4-port, 8-port desktop models.
- ▶ 4-port, 8-port models in 19" rack mount chassis (1U).
- ▶ Optional 19" rack mounting brackets for desktop models (1U).
- ▶ Optional rack mount extensions for 24" racks.
- ▶ Dedicated keyboard and mouse emulator for each PC to ensure flawless boot up and operation.
- ▶ Multi-platform-mix PC, Mac, Sun, Alpha®, RS/6000®, HP®9000, SGI®, ASCII devices; also USB support.
- ▶ Support of any mix of computers – Windows® NT, Windows 2000, Novell® 4.x, UNIX®, Linux, or OpenVMS®.
- ▶ Easy to manage, tangle-proof, high-resolution PC cables.
- ▶ Supports VGA, SVGA, XGA high resolution video – 1600x1200.
- ▶ Hot-key commands or individual channel buttons on front panel for convenient operation.
- ▶ IntelliMouse® support.
- ▶ SCAN for effortless monitoring.
- ▶ SKIP to filter unused channels.

Specifications

CS2 (2-port) CS4 (4-port)	
Dimensions	268mm (W) x 200mm (D) x 44mm (H)
Weight	1,62 kg
Power	No external power required

CS8 (8-port)	
Dimensions	390mm (W) x 200mm (D) x 44mm (H)
Weight	2,24 kg
Power	No external power required

CS4R (4-port rack mount with cable support bracket) CS8R (8-port rack mount with cable support bracket)	
Dimensions	485mm (W) x 333mm (D) x 44mm (H)
Weight	2,8 kg
Power	No external power required

Optional DC Adapter - 6V/1.4A

Warranty: Two Years In addition Raritan offers two years extended warranty.

Ready to manage smarter? Do it with Raritan's CompuSwitch
Call +31-10-2844040 or visit Raritan.eu/CompuSwitch

Raritan is a leading supplier of solutions for managing IT infrastructure equipment and the mission-critical applications and services that run on it. Raritan was founded in 1985, and since then has been making products that are used to control millions of servers at more than 50.000 network data centers, computer test labs and multi-workstation environments around the world. From the small business to the enterprise, Raritan's complete line of compatible and scalable KVM and remote connectivity products offers IT professionals the most reliable, flexible and secure in-band and out-of-band solutions to manage data center equipment applications and services, while improving operational productivity. More information on the company is available at Raritan.eu

©2009 Raritan Computer, Inc. Raritan, CompuSwitch, Cat5 Reach and FiberReach are registered trademarks of Raritan Computer, Inc.; Sun is a registered trademark of Sun Microsystems, Inc.; Windows and IntelliMouse are registered trademarks of Microsoft Corp.; Novell is a registered trademark of Novell, Inc.; UNIX is a registered trademark of UNIX System Laboratories, Inc.; PS/2 and RS/6000 is a registered trademark of IBM Corporation; HP9000 is a registered trademark of Hewlett-Packard Development Company, L.P.; Mac is a registered trademark of Apple Computers, Inc.; Alpha is a registered trademark of Digital Equipment Corp.; OpenVMS is a registered trademark of Compaq Information Technologies Group, L.P. and CPQ Holdings, Inc.; SGI is a registered trademark of Silicon Graphics, Inc.