



EZswitch Combo KVM Series

How well is your business equipped for a disruption in IT operations?

As a growing small or medium-sized business, the key to your success lies in being able to quickly and effectively react to situations that disrupt your company's uptime. With the expreZ^o™ EZswitch, you can access and control computers that require rebooting or troubleshooting, ensuring business continuity.



- Easy to install and setup
- All-in-one compact design
- Video resolution support of up to 2048 x 1536
- PS/2 and USB ports (keyboard and mouse) for local access

E-mail: marketing.europe@raritan.com

8- and 16-port Combo KVM Switch

Features

- Connect computers via PS/2 and/or USB.
- Supports Windows, Linux, Mac OS9/OSX, Sun Microsystems.
- On-Screen-Display (OSD) & Cascade Chain functions.
- OSD with intuitive menus for quick and effective navigation.
- Daisy chain switches to control up to 4096 PCs (16-Port) from a single console. Cascaded units do not need special configuration.
- Hot-pluggable: all devices connected to expreZo can be added or removed at any time without shutting down the devices.
- Auto Scan video for effortless monitoring.
- Easily switch between connected devices with:
 - Hardware Push Button,
 - Hot-Keys on PS/2 and/or USB keyboard,
 - OSD menu.
- Supports LED display for PC and/or server status monitoring.
- Supports video resolutions up to 2048 x 1536.
- Enable/disable beeper during channel switching.
- Supports tiering with Dominion® KX2 models.
- Rack mountable in 19" rack (1U).
- Firmware is upgradeable via a mini-USB port.

System Requirements

Local Console

Supports VGA, SVGA, Multisync monitor high resolution video - 2048x1536.
PS/2 and/or USB Keyboard/Mouse.

Computer or Server

PCs must support:
- VGA, SVGA or Multisync card.
- Type A USB port or mini-DIN 6 pin PS/2 keyboard and mouse.

Cables

Custom 4-in-1 cables included in the product package.

Specification

Models:	EZ-108 (8-port) / EZ-116 (16-port)	
Selection Method	Push Button and Hot-Key (PS/2 / USB Keyboard) Or On-Screen-Display (OSD)	
LEDs	Red for PC Selection Green for PC On-Line ready	
KVM Ports	Video (KB/MS)	8/16 x HDB-15 female (PS/2 & USB signal combined)
Console Ports	Keyboard	1 x 6 pin mini-DIN female
	Mouse	1 x 6 pin mini-DIN female
	Video	1 x HDB-15 female
	Keyboard	1 x USB – A type female
	Mouse	1 x USB – A type female
Auto-Scan Interval	Adjustable time setting by OSD menu driven	
DDC, DDC2 monitor	Max. Resolution up to 2048x1536@65Hz	
Hot Swappable	Yes	
Operating systems supported	Windows 98SE/ME/2000/XP/2003/Vista/7 Server, Linux, Mac OS9/OSX and Sun Microsystems.	
Power	External power adapter, DC 5V, 2.0A	
Dimensions (L X W X H)	44 x 15.7 x 4.5 cm (17.3 x 6.1 x 1.5 inch)	
Unit Weight	1750g / 1900g	
Housing material	Metal	
Operating Temperature	32~122°F (0~ 50°C)	
Humidity	0%~80%RH	
Firmware upgrade port	Mini USB female	



©2011 Raritan Inc. All rights reserved. Raritan®, Dominion®, expreZo™ are registered trademarks of Raritan Inc. or its wholly-owned subsidiaries. All others are registered trademarks or trademarks of their respective owners.