

# Mounting Brackets

## SECURELY SEAT RACK MOUNTED POWER DISTRIBUTION DEVICES

Raritan Mounting Brackets ease the installation and securing of Raritan power distribution products into racks, IT cabinets, and other structures. Compatible with Raritan rack power distribution units (PDUs), inline meters, rack transfer switches, smart rack controllers, and branch circuit monitoring systems, these Mounting Brackets can be used vertically or horizontally to increase mounting flexibility and solve instrumentation challenges.

### Bracket Options Include


- L or Angle Mounting Brackets join two parts at a 90-degree angle, providing more consistent straight corners to support both vertical and horizontal mounting positions
- Hinge Mounting Brackets combine two parts at various adjustable angles/pitches to support vertical and horizontal mounting positions
- Vertical Mounting Brackets are molded into either a Flat, S-shape, or U-shape to support varied vertical mounting positions
- Specialized Mounting Brackets are molded to resolve specific mounting scenarios



## BENEFITS

- Versatile for use in racks, IT cabinets, and other structures
- Bracket options support vertical and horizontal mounting positions
- Constructed of heavy steel to ensure strength and durability
- Meets RoHS Directives material restrictions
- Molded into various shapes to address common mounting and instrumentation challenges
- Designed with functional holes to ease tool-less button mounting and secure screws


# L OR ANGLE MOUNTING BRACKETS



**250-70-0094-00**

Dimensions (WxDxH):  
930mm x 436mm x 38mm


Extended-width L Bracket with small-sized U-shaped and extended length U-shaped holes to mount 0U PDUs.



**250-80-0021-00**

Dimensions (WxDxH):  
210mm x 436mm x 30mm


Extended-width L Bracket with keyhole and small-sized U-shaped holes to mount two 0U PDUs side-by-side.



**250-80-0040-00**

Dimensions (WxDxH):  
175mm x 43mm x 52mm

Extended-width L Bracket with rounded holes to mount 0U PDUs.



**250-80-0046-00**

Dimensions (WxDxH):  
52.2mm x 25.5mm x 48.8mm


L Bracket with rounded and small-sized U-shaped holes to mount a PDU with outlets facing inward or outward.



**250-80-7758-00**

Dimensions (WxDxH):  
43mm x 59mm x 65mm

Extended-width L Bracket with teardrops and small-sized U-shaped holes to mount two PDUs side-by-side.



**251-01-0034-00**

Dimensions (WxDxH):  
50mm x 43mm x 43mm


L Bracket with rounded, small-sized U-shaped, and extended-length U-shaped holes to mount 0U PDUs.



**251-01-0036-00**

Dimensions (WxDxH):  
88mm x 59mm x 30mm


L Bracket with square, teardrops, rounded, and small-sized U-shaped holes to mount 0U PDUs facing the side of a cabinet.



**251-01-0039-00**

Dimensions (WxDxH):  
486mm x 44mm x 10mm

L Bracket with rounded holes to mount 0U PDUs.



**251-01-0055-00**

Dimensions (WxDxH):  
60mm x 40mm x 70mm

L Bracket with rounded and extended-length U-shaped holes to mount 0U PDUs.

# L OR ANGLE MOUNTING BRACKETS


**MOST COMMON**



**251-01-0056-00**

Dimensions (WxDxH):  
103mm x 38mm x 43.6mm


L Bracket with small-sized and extended-length U-shaped holes to mount 0U PDUs.



**251-01-0102-00**

Dimensions (WxDxH):  
93mm x 40mm x 50mm


L Bracket with rounded and small-sized U-shaped holes to extend the height of a PDU.



**251-01-0104-00**

Dimensions (WxDxH):  
95mm x 75mm x 60mm

L Bracket with rounded and extended-length U-shaped holes to mount a single PDU.




**251-02-0011-00**

Dimensions (WxDxH):  
53.2mm x 43.6mm x 21.3mm

L Bracket with rounded, small-sized U-shaped and extended-length U-shaped holes to extend the height of a PDU.


# HINGE MOUNTING BRACKETS



**251-01-0054-00**

Dimensions (WxDxH):  
83.4mm x 68.2mm x 53.6mm

Hinge Bracket with squared and extended-length U-shaped holes to mount a single PDU.




**251-01-0068-00**

Dimensions (WxDxH):  
108.2mm x 159.5mm x 142.5mm

Hinge Bracket with two hinge joints and teardrops, small-sized U-shaped, and extended-length U-shaped holes to mount a single PDU.


# VERTICAL MOUNTING BRACKETS



**250-75-0006-00**

Dimensions (WxDxH):  
208mm x 81mm x 18mm


Extended-width S-shaped Vertical Bracket with teardrops and small-sized U-shaped holes to mount two 0U PDUs side-by-side.



**250-80-0012-00**

Dimensions (WxDxH):  
142mm x 88mm x 14.6mm


U-shaped Vertical Side-by-Side Bracket with teardrops and rounded holes to mount two 0U PDUs side-by-side.



**250-80-0049-00**

Dimensions (WxDxH):  
136.5mm x 65mm x 1.6mm

Flat Vertical Bracket with teardrops and small-sized U-shaped holes to mount 0U PDUs.



**251-01-0018-00**

Dimensions (WxDxH):  
131.3mm x 81mm x 35mm


S-shaped Vertical Bracket with teardrops and small-sized U-shaped holes to mount two 0U PDUs side-by-side.



**251-01-0021-00**

Dimensions (WxDxH):  
131.3mm x 81mm x 14.7mm


S-shaped Vertical Bracket with teardrops and small-sized U-shaped holes to mount two PDUs side-by-side.



**251-01-0025-00**

Dimensions (WxDxH):  
66mm x 64mm x 22mm


S-shaped Vertical Bracket that occupies 1U of EIA\* mounting space with teardrops and small-sized U-shaped holes.



**251-01-0026-00**

Dimensions (WxDxH):  
66mm x 64mm x 22mm


S-shaped Vertical Bracket that occupies 1U of EIA\* mounting space with teardrops and small-sized U-shaped holes.



**251-01-0028-00**

Dimensions (WxDxH):  
53.2mm x 34mm x 20mm

S-shaped Vertical Bracket with small-sized U-shaped and extended-length U-shaped holes to mount 0U PDUs with outlets facing inward or outward.




**251-01-0029-00**

Dimensions (WxDxH):  
125.3mm x 110mm x 15mm

U-shaped Vertical Side-by-Side Bracket with teardrops and rounded holes to mount two 0U PDUs side-by-side.

\*Electronic Components Industry Association, EIA Standards Committee


# VERTICAL MOUNTING BRACKETS



**251-01-0032-00**

Dimensions (WxDxH):  
142mm x 12mm x 88mm


U-shaped Vertical Side-by-Side Bracket with keyhole and rounded holes to mount two 0U PDUs side-by-side.



**251-01-0070-00**

Dimensions (WxDxH):  
131.3mm x 19mm x 81mm

S-shaped Vertical Bracket with teardrop and extended-length U-shaped holes to mount two 0U PDUs side-by-side.




**251-01-0092-00**

Dimensions (WxDxH):  
244.5mm x 43.6mm x 2mm

Flat Vertical Side-by-Side Bracket with rounded and extended-length U-shaped holes.


# SPECIALIZED MOUNTING BRACKETS



**251-01-0086-00**

Dimensions (WxDxH):  
100mm x 2mm x 82mm


Specialized flat bracket with rounded and small-sized U-shaped holes to mount PDUs in Legrand's Minkels Varicon-M cabinets.



**A0026-000001-000-1**

Dimensions (WxDxH):  
78.31mm x 9.9mm x 86.9mm


Specialized Bracket with rounded and small-sized U-shaped holes to mount PDUs in Legrand's Nexpan cabinets.



**A0026-000002-000-1**

Dimensions (WxDxH): 153.31mm x 9.9mm x 86.9mm

Specialized Bracket with rounded and small-sized U-shaped holes to mount PDUs in Legrand's Nexpan cabinets.



**251-02-0023-00**


Dimensions (WxDxH):  
225mm x 68.7mm x 45.8mm

Specialized two-post bracket for mounting shallow rack transfer switches.


# MOUNTING BRACKET KITS

## G2-RACK-FOR-ZU


Bracket Kit used to mount 0U PDUs.



1 x Flat Vertical Bracket  
(250-70-0007-00)  
Dimensions (WxDxH):  
85.2mm x 43.6mm x 3mm



1 x Plastic Sliding Bracket  
(252-67-0029-00)  
Dimensions (WxDxH):  
52mm x 13mm x 67mm




1 x L Bracket  
(250-70-0093-01)  
Dimensions (WxDxH):  
38mm x 53mm x 43mm




1 x High-Strength  
Plastic M5 Button Mount  
(250-80-0011-00)

## G3-RACK-FOR-ZU


Bracket Kit used to mount 0U PDUs.




1 x Flat Vertical Bracket  
(250-70-0007-00)  
Dimensions (WxDxH):  
85.2mm x 43.6mm x 3mm



1 x Plastic Sliding Bracket  
(250-70-0106-00)  
Dimensions (WxDxH):  
52mm x 13mm x 67mm




1 x L Bracket  
(250-70-0093-01)  
Dimensions (WxDxH): 38mm x  
53mm x 43mm




1 x High-Strength  
Plastic M5 Button Mount  
(250-80-0011-00)

## G4-HOLDER-FOR-ZU

Bracket Kit used to mount 0U PDUs.



2 x Metal Button Screw  
(250-70-0140-00)




2 x Flat Vertical Bracket  
(250-70-0141-00)  
Dimensions (WxDxH):  
35mm x 3mm x 40mm


# MOUNTING BRACKET KITS

## RACK-FOR-ZU


Bracket Kit used to mount DPX-xxx and PX-xxx 0U PDUs.




1 x Flat Vertical Bracket  
(250-70-0007-00)  
Dimensions (WxDxH):  
85.2mm x 43.6mm x 3mm



1 x Pin Bracket  
(250-80-0009-00)  
Dimensions (WxDxH):  
43.6mm x 6.6mm x 3.2mm



1 x Holder  
(250-80-0008-00)  
Dimensions (WxDxH):  
61.46mm x 43.6mm x 16mm




1 x L Bracket  
(250-70-0093-01)  
Dimensions (WxDxH):  
38mm x 53mm x 43mm



1 x High-Strength  
Plastic M5 Button Mount  
(250-80-0011-00)

## RACK-KIT-DPX-1U

Bracket Kit used to mount 1U PDU in a 19" cabinet.




1 x L Bracket  
(250-80-0123-00)  
Dimensions (WxDxH):  
305.48mm x 43.6mm x 21.3mm



1 x Cable Management Bracket  
(250-80-0125-00)  
Dimensions (WxDxH):  
447.6mm x 12.4mm x 8mm

## RACK-KIT-PX-2U

Bracket Kit used to mount 2U PDU in a 19" cabinet.



1 x L Bracket  
(250-70-3017-00)  
Dimensions (WxDxH):  
365.23mm x 88.1mm x 21.3mm



1 x Cable Management Bracket  
(250-70-3018-00)  
Dimensions (WxDxH):  
447.6mm x 12.4mm x 8mm

Part Number	Bracket Type	Dimensions (W x D x H)	Model Compatibility	
			Raritan PX3 Models	Raritan PX4 Models
250-70-0094-00	L Bracket	930mm x 436mm x 38mm	✓	
250-80-0021-00	L Bracket	210mm x 436mm x 30mm	✓	
250-80-0040-00	L Bracket	175mm x 43mm x 52mm	✓	
250-80-0046-00	L Bracket	52.2mm x 25.5mm x 48.8mm	✓	
250-80-7758-00	L Bracket	43mm x 59mm x 65mm	✓	
251-01-0034-00	L Bracket	50mm x 43mm x 43mm	✓	
251-01-0036-00	L Bracket	88mm x 59mm x 30mm	✓	✓
251-01-0039-00	L Bracket	486mm x 44mm x 10mm	✓	
251-01-0055-00	L Bracket	60mm x 40mm x 70mm	✓	
251-01-0056-00	L Bracket	103mm x 38mm x 43.6mm	✓	
251-01-0102-00	L Bracket	93mm x 40mm x 50mm	✓	
251-01-0104-00	L Bracket	95mm x 75mm x 60mm	✓	✓
251-02-0011-00	L Bracket	53.2mm x 43.6mm x 21.3mm	✓	
251-01-0054-00	Hinge Bracket	83.4mm x 68.2mm x 53.6mm	✓	
251-01-0068-00	Hinge Bracket	108.2mm x 159.5mm x 142.5mm	✓	
250-75-0006-00	Vertical Bracket	208mm x 81mm x 18mm	✓	✓
250-80-0012-00	Vertical Bracket	142mm x 88mm x 14.6mm	✓	✓
250-80-0049-00	Vertical Bracket	136.5mm x 65mm x 1.6mm	✓	
251-01-0018-00	Vertical Bracket	131.3mm x 81mm x 35mm	✓	
251-01-0021-00	Vertical Bracket	131.3mm x 81mm x 14.7mm	✓	
251-01-0025-00	Vertical Bracket	66mm x 64mm x 22mm	✓	✓
251-01-0026-00	Vertical Bracket	66mm x 64mm x 22mm	✓	✓
251-01-0028-00	Vertical Bracket	53.2mm x 34mm x 20mm	✓	
251-01-0029-00	Vertical Bracket	125.3mm x 110mm x 15mm	✓	
251-01-0032-00	Vertical Bracket	142mm x 12mm x 88mm	✓	✓
251-01-0070-00	Vertical Bracket	131.3mm x 19mm x 81mm	✓	
251-01-0092-00	Vertical Bracket	244.5mm x 43.6mm x 2mm	✓	
251-01-0086-00	Specialized Bracket	100mm x 2mm x 82mm	✓	
A0026-000001-000-1	Specialized Bracket	78.31mm x 9.9mm x 86.9mm	✓	
A0026-000002-000-1	Specialized Bracket	153.31mm x 9.9mm x 86.9mm	✓	
251-02-0023-00	Specialized Bracket	225mm x 68.7mm x 45.8mm	✓	
G2-RACK-FOR-ZU	Bracket Kit	Dimensions listed above	✓	
G3-RACK-FOR-ZU	Bracket Kit	Dimensions listed above	✓	
G4-HOLDER-FOR-ZU	Bracket Kit	Dimensions listed above		✓
RACK-FOR-ZU	Bracket Kit	Dimensions listed above	✓	
RACK-KIT-DPX-1U	Bracket Kit	Dimensions listed above	✓	✓
RACK-KIT-PX-2U	Bracket Kit	Dimensions listed above	✓	✓
RACK-KIT-PX3TS-1U	Bracket Kit	Dimensions listed above	✓	

Packaging Notes: One (1) mounting bracket is included per package unless a Mounting Bracket Kit is purchased where multiple bracket types are included. Bracket assembly screws are included, where necessary. Cage nuts are not included.

**Raritan.com/mountingbrackets**

800-724-8090 | sales@raritan.com

©2023 Legrand®. All rights reserved. The industry-leading brands of Approved Networks, Ortronics, Raritan, Server Technology, and Starline empower Legrand's Data, Power & Control to produce innovative solutions for data centers, building networks, and facility infrastructures. Our division designs, manufactures, and markets world-class products for a more productive and sustainable future. The exceptional reliability of our technologies results from decades of proven performance and dedication to research and development. V1315R6