

# Compatibility Matrix

## CommandCenter<sup>®</sup> Secure Gateway Release 4.2.0

*Review the Release Notes document for important release information. Consult the Quick Setup Guide, Deployment Guide, and Admin Guide for product setup instructions, implementation, and operations. Documents and firmware downloads can be located on the enclosed document CD-ROM and on the Raritan website at [www.raritan.com/support/](http://www.raritan.com/support/)*

### I. Compatibility Matrix

*It is important that you upgrade any listed Raritan products to the specified versions indicated below.*

CommandCenter Secure Gateway firmware information:

| RARITAN PRODUCTS  | FIRMWARE VERSION | SHIPS WITH  |
|---|------------------|---|
| <b>CommandCenter Secure Gateway:</b><br><b>CC-SG E1</b><br><b>CC-SG V1</b>  | 4.2.0            | Raritan Remote Client (RRC) 4.6.8<br>Multi Platform Client (MPC) 6.0.1<br>Raritan Console (RC) 2.7.20<br>Raritan Serial Console (RSC) 3.0.0 |
| <b>Important note</b> for CC-SG customers: CC-G1 hardware cannot be upgraded with this firmware version. A CC-G1 upgrade attempt will fail without damaging the G1 unit or database. Review CC-SG 4.0.0 or 4.1.0 Release Notes to learn about different methods for determining the hardware version. |                  |   |

Firmware version of CC-SG can be located under Help→About Raritan CommandCenter.

Firmware versions of all Raritan devices can be verified by running a CC-SG Device Asset Report.

CommandCenter Secure Gateway has been tested against the following Raritan product versions and against supported client applications specified below.

| RARITAN PRODUCTS SUPPORTED   |  | SUPPORTED FIRMWARE VERSIONS |          |
|------------------------------|--|-----------------------------|----------|
| Product Name/Model           | Part #   | Current                     | Previous |
| Dominion KX II               | DKX2-108, DKX2-116, DKX2-216, DKX2-232, DKX2-416, DKX2-432, DKX2-132, DKX2-464 | 2.1.10                      | 2.1.0    |
| Dominion KX II               | DKX2-832, DKX2-864   | 2.1.10                      | 2.1.8    |
| Dominion KX                  | DKX116, DKX216, DKX232, DKX416, DKX432, DKX132, DKX464                         | 1.4.9                       | 1.4.8    |
| Dominion KX II               | DKX2-101   | 2.0.20                      | 2.0.0    |
| Dominion KX                  | DKX101   | 1.1.1                       | 1.1.0    |
| Dominion SX (Intel platform) | All Models * <sup>1</sup>  | N/A                         | N/A      |
| Dominion SX (MIPS platform)  | DSX4, DSX8, DSXA16, DSXA32, DSXA48   | 3.1.7                       | 3.1.6    |
| Dominion KSX II              | DKSX2-144, DKSX2-188   | 1.0                         | N/A      |

| RARITAN PRODUCTS SUPPORTED             |   | SUPPORTED FIRMWARE VERSIONS |          |
|--|---|-----------------------------|----------|
| Product Name/Model                     | Part #  | Current                     | Previous |
| Dominion KSX                           | DKSX440, DKSX880  | 3.6                         | 3.24     |
| IP-Reach M1/M2 and, IP-Reach TR-Series | IPR-M1, IPR-M2, IPR-TR364   | 3.6                         | 3.5      |
| Paragon II System Controller           | P2-SC   | 1.2.0.5.13                  | N/A      |
| CommandCenter NOC                      | CC-NOC 100, 250, 2500 M/N/S   | N/A                         | N/A      |
| Dominion PX* <sup>2</sup>              | DPCSxxx* <sup>4</sup> , DPCRxxx* <sup>4</sup> , DPXSxxx* <sup>3</sup> | 1.3.5                       | 1.3.1    |
| PCR Power Strips                       | PCR8, PCR12, PCR18, PCR20   | N/A                         | N/A      |

\*<sup>1</sup> SX Intel models are not supported.

\*<sup>2</sup> Dominion PX firmware versions listed in this Compatibility Matrix are required for direct connectivity to CC-SG via IP modes. For Dominion PX firmware versions required in 'managed power strip' mode (when Dominion PX connection to a Dominion device via a power CIM or power cable) refer to the documentation of the Dominion device managing the PX for special instructions.

\*<sup>3</sup> xxx represents 3 alphanumeric values that would be different for each model in the product category.

CC-SG node interfaces are available for the following products:

| OTHER PRODUCTS SUPPORTED | SUPPORTED VERSIONS             |
|--------------------------|--------------------------------|
| VMware™ Virtual Center   | 2.5                            |
| VMware™ ESX              | 3.0, 3.5                       |
| VMware™ ESXi             | Not supported for this release |
| iLO2                     | 1.61                           |
| iLO                      | 1.89                           |
| RILOE                    | 2.52                           |
| RILOE II                 | 1.21                           |
| DRAC4                    | 1.35 (Build 09.27), 1.50       |
| RSA II                   | 1.05                           |
| IPMI                     | 1.5, 2.0                       |
| Web browser              | See table below                |
| Telnet                   | 1.0                            |
| RDP                      | 1.1                            |
| VNC                      | 1.0.1                          |
| SSH                      | 1.0.1                          |

CC-SG Admin Client (Java) and Access Client (HTML) are supported in the following environments:

| CLIENT PLATFORMS            | SUPPORTED BROWSERS  | SUN JRE* <sup>1</sup> SUPPORT                                      |
|-----------------------------|---|--|
| Windows Vista* <sup>2</sup> | Internet Explorer 7.0, 8.0 (64 bit only);<br>Firefox 2.0, 3.0.x (3.0.10 recommended / 3.0.11 not supported) | 1.5.0_10, 1.5.0_12, 1.6.0_05, 1.6.0_07, and 1.6.0_10 thru 1.6.0_13 |
| Windows XP* <sup>2</sup>    | Internet Explorer 6.0, 7.0, 8.0; Firefox 2.0, 3.0.x (3.0.10 recommended / 3.0.11 not supported)             | Same as above  |
| Windows 2000                | Internet Explorer 6.0; Firefox 2.0, 3.0.x (3.0.10 recommended / 3.0.11 not supported)                       | Same as above  |
| Red Hat EL 4, 5             | Firefox 2.0, 3.0.x (3.0.10 recommended / 3.0.11 not supported)  | Same as above  |
| SUSE 10                     | Firefox 2.0, 3.0.x (3.0.10 recommended / 3.0.11 not supported)  | Same as above  |
| Solaris 10                  | Firefox 2.0, 3.0.x (3.0.10 recommended / 3.0.11 not supported)  | Same as above  |
| Fedora Core 7, 8            | Firefox 2.0, 3.0.x (3.0.10 recommended / 3.0.11 not supported)  | Same as above  |
| MacOS 10.4, 10.5            | Firefox 2.0, 3.0; Safari 2.0, 3.0.10, 3.0.11  | Same as above  |

\*<sup>1</sup> CC-SG release 4.1.0 has been tested to be compatible with these specific versions of Sun JRE and is not supported for use with other versions. Sun JRE can be found at <http://java.sun.com/j2se/>.

If using Windows and using the client applet, JRE will only work with Windows 32 bit. See <http://java.sun.com/javase/6/webnotes/install/system-configurations.html> for Java support information.

\*<sup>2</sup> both 32 and 64 bit OS editions are supported

CLI access to CC-SG is supported in the following environments:

| CLIENT APPLICATIONS | SUPPORTED VERSIONS                   |
|---------------------|--------------------------------------|
| SSH                 | PuTTY version 0.58 or later, OpenSSH |