

RACKMOUNT LCD CONSOLES

Features & Benefits

FEATURE	BENEFIT
1U RACK-MOUNT UNIT	<ul style="list-style-type: none"> ▪ Saves space at the rack. The 1U design takes up to 85% less space than a full-size keyboard, monitor, and mouse.
LED-BACKLIT LCD DISPLAY	<ul style="list-style-type: none"> ▪ The LED KVM consoles' energy efficient LED-backlit LCD display reduces energy consumption 20-50% over current LCD cold cathode fluorescent (CCFL) backlit technology. The LED-backlit technology also provides for better contrast and brightness, greater color range, a more rapid response to changes in scene, and more accurate image rendering for a clean, crisp display.
SUPPORTS DIGITAL AND ANALOG VIDEO	<ul style="list-style-type: none"> ▪ The LED KVM consoles support digital video inputs (HDMI/DP/DVI) for high definition video as well as a traditional VGA input. Perfect to connect to the DVI-D local port of the Dominion KX III KVM-over-IP switch family and MasterConsole Digital CAT5 KVM switches.
HIGH RESOLUTION VIDEO DISPLAY	<ul style="list-style-type: none"> ▪ 17 Inch T1700G2-LED: 16:9 widescreen display supports up to 1080P, 1920x1080@60Hz. ▪ 19 Inch T1900-LED: 4:3 screen supports up to 1280x1024@75Hz.
COMPATIBLE WITH RARITAN KVM SWITCHES	<ul style="list-style-type: none"> ▪ Dominion DKX3 series (except DKX4-101) ▪ Dominon SX2 series ▪ MasterConsole Digital Series ▪ CommandCenter® Secure Gateway
INTEGRATED MICRO SWITCH FOR AUTO POWER ON/OFF	<ul style="list-style-type: none"> ▪ Features an integrated micro switch for auto power on/off when opening and closing the monitor below a 20 degree angle to ensure the maximum useful life of the LCD panel.
BUILT-IN USB 3.0 & 2.0 PASS THRU PORT	<ul style="list-style-type: none"> ▪ Enables convenient, front-of-the-rack media connections to external keyboard, mouse or smart card reader for management of Raritan KVM switches directly from the racks in which they are installed.

**SIDE RAILS WITH FIXED POSITION
FEATURE**

- Stable working surface prevents unwanted drawer movement

SIMPLE INSTALLATION

- Easily install the LED KVM console in the rack using plug-and-play auto-configuration and easy-to-use, on-screen displays

BUILT-IN POWER SUPPLY

- Eliminates the need for external power bricks

**SUPPORTS WINDOWS®, LINUX® AND
OTHER OPERATING SYSTEMS**

- Integrates into virtually any server room or data center environment

**MULTI-LANGUAGE KEYBOARD
SUPPORT**

- Supports US English, UK English, French, German, Swiss German, Italian, Japanese, Russian, Spanish, and Turkish

To learn more visit

www.raritan.com