



HIGH PERFORMANCE IP KVM SWITCH ACCESS

The Dominion® KX III User Station is a standalone appliance for high performance IP access to servers connected to Dominion® KX III switches, access via RDP, VNC, and SSH, as well as optional CommandCenter integration. It can sit on a desk, be mounted in a standard 19" rack, or VESA-mounted on the back of a monitor. Deploy it using standard Cat5 cabling and Ethernet/IP technology. Simultaneously access, view, and control multiple servers, spread across single or dual monitors. Web-based remote control of User Stations connected to wall monitors in studios and control rooms.

The User Station can replace outdated analog matrix switches, supplement inflexible broadcast systems or be deployed anywhere hassle-free IP access is needed. It's perfect for broadcast labs, studios, control rooms, offices, and data centers.

APPLICATIONS

- Broadcast Labs & Studios
- Control Rooms
- Government & Military
- Transportation & Energy
- Factory & Industrial
- Data Centers

HIGH PERFORMANCE USER APPLIANCE

- Powerful Intel-based platform
- Two 1080p streaming video sessions at 30 FPS
- Ultra-fast connections and sub-second switching with the non-blocking DKX3-808 model
- Supports VGA, DVI, HDMI & DisplayPort video
- Self-contained, low maintenance appliance

PRODUCTIVE AND POWERFUL USER INTERFACE

- Supports single or dual monitors
- 8 or more simultaneous IP connections
- Scan & monitor servers
- Full Screen mode
- Favorites and hot-key switching
- Virtual media and USB audio
- Matrix server view
- Productive window management. Save & restore window layouts.

FLEXIBLE AND EASY TO DEPLOY

- Flexible dual LAN or WAN access
- Use corporate and/or separate LAN
- Connects with Cat5 cabling
- Access hundreds of servers and devices
- PC/Laptop access also available
- Desktop, rack & VESA mountable
- CommandCenter for centralized login and access
- Support for RDP, VNC, and SSH connections

Specifications	
Hardware	Intel Celeron CPU, 4GB RAM, 64GB Solid State Disk
Video	Single or Dual Display, One HDMI, Two DisplayPort. Up to 4K desktop.
Network	Dual Gigabit Ethernet Ports, IPv4, IPv6, DHCP or static address
Power	Input: 100-240V AC, Output: 19V 4.47A DC, 65W Max
USB	6 USB 2.0, 2 USB 3.0 for keyboard, mouse, audio & virtual media
Audio	Microphone In, Speakers Out
Certifications	FCC/CE/VCCI/cUL/CB
Dimension	190(L) x 165(W) x 43(H) mm
Weight	1.4 Kg. 2.3 Kg shipping weight.
Rack Mount	Desktop, VESA & Optional 1U bracket
Temperatures, Humidity	0-40 degrees Celsius. Non-condensing 10-90% humidity.
Vibration, Altitude	1-200Hz, 1.146 Grms random vibration. Max altitude 2,000 meters.




Front View

1. Microphone Input
2. Audio Output
3. Power LED
4. Hard Disk LED
5. Power Button
6. USB 2.0 Ports

Rear View

7. DC Power Input
8. Dual Gigabit LAN
9. USB 3.0 Ports
10. USB 2.0 Ports
11. DisplayPort (DP) Video
12. HDMI Video

HOW DOES IT WORK?



EASY TO DEPLOY

1. Attach single or dual monitors
2. Attach keyboard and mouse
3. Optionally attach speakers, smart card, and virtual media
4. Connect to corporate or separate LAN
5. Configure to add users and KX III's, or use with CommandCenter for centralized login and access
6. Access and control servers connected to the KX III switches and access equipment via RDP, VNC, & SSH

Visit www.raritan.com/user-station
or Call 1.800.724.8090 for more information.

©2019 Raritan Inc. All rights reserved. Raritan® is a registered trademarks of Raritan Inc. or its wholly-owned subsidiaries. All others are registered trademarks or trademarks of their respective owners. Raritan began developing KVM switches for IT professionals to manage servers remotely in 1985. Today, as a brand of Legrand, we are a leading provider of intelligent rack PDUs. Our solutions increase the reliability and intelligence of data centers in 9 of the top 10 Fortune 500 technology companies. Learn more at Raritan.com V1216R4

Raritan
A brand of **Legrand**